

Carbonyl Sulfide COS

Cylinder Pressure 2000 psig (138 bar)
 Cylinder Valve Outlet CGA No. 330
 DOT/TC Label Nonflammable
 Other Available Sizes SCOTTY™ Transportable

Recommended Equipment
 Two-Stage Regulator Model 215, Page 271
 Single-Stage Regulator Model 213, Page 271

in Nitrogen				Single-Certified Standards	
				Certified	
Concentration	Size	Contents		Master Class	Working Class
		CF	m ³		
ACULIFE 0.1 – 0.9 ppm	30AL	140	4		•
	16AL	74	2		•
	7AL	28	0.8		•
ACULIFE 1 – 9 ppm	30AL	140	4	•	•
	16AL	74	2	•	•
	7AL	28	0.8	•	•
ACULIFE 10 – 49 ppm	30AL	140	4	•	•
	16AL	74	2	•	•
	7AL	28	0.8	•	•
ACULIFE 50 – 999 ppm	30AL	140	4	•	•
	16AL	74	2	•	•
	7AL	28	0.8	•	•
ACULIFE 0.1 – 3%	44	209	6	•	•
	16	82	2	•	•
	7	32	0.9	•	•

Carbonyl sulfide calibration standards are also available in hydrocarbon balance gases. Contact your Air Liquide representative for more information.